















More information on the website  
[radwag.com/en/info,w1,BS1](http://radwag.com/en/info,w1,BS1)

# MA 200/1.5Y.WH Moisture Analyzer



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Statistics
-  IR sensors
-  GLP Procedures
-  Replaceable unit
-  Statistical Quality Control
-  ALIBI Memory
-  Drying modes
-  Samples drying
-  Moisture content analysis
-  Dry mass determination
-  Wi-Fi

## Datasheet

Metrological parameters	
Maximum capacity [Max]	200 g
Readability [d]	0.1 mg
Tare range	-200 g
Adjustment	external
Maximum sample weight	200 g
Heating module	halogen
Moisture content repeatability	+/-0.05% (sample ~ 2g), +/-0.01% (sample ~ 10g)

<b>Metrological parameters</b>	
Moisture content readability	0.0001%
Drying temperature range	Max 250 °C
<b>Physical parameters</b>	
Leveling system	semi-automatic - LevelSENSING
Display	10" graphic colour touchscreen
Weighing chamber	automatic
Maximum sample height	20 mm
Weighing pan dimensions	ø90, h= 8 mm
Packaging dimensions	540×610×470 mm
Net weight	5.3 kg
Gross weight	6.8 kg
<b>Construction</b>	
Protection class	IP 43
<b>Features of use</b>	
Display mode	%MC, %DC, %ATRO MC, %ATRO DC, g, g/kg MC, g/kg DC, -%MC
Drying method	4 drying profiles (standard, fast, step, mild)
Finish mode	4 modes (automatic, manual, time-defined, user-defined)
Additional functions	sample traceability
<b>Communication interface</b>	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
<b>Electrical parameters</b>	
Power supply	100V – 120V AC 50/60Hz or 200V-240V AC 50/60Hz
Power consumption	6 W
Heating module power	450 W
<b>Environmental conditions</b>	
Operating temperature	+10 ÷ +40 °C
<b>SOP – metrological tests</b>	
Mass indication control	External mass standard 50 g, 100 g, 200 g (depending on the type of moisture analyzer)
Mass indication control	External mass standard 50 g, 100 g, 200 g (depending on the type of moisture analyzer)
Internal adjustment	For .IC models only, GLP report
External adjustment	For all models, GLP report
Drying temperature control	One- or two-point, depending on the drying profile (equipment: GT105k-12/Z Control Thermometer)
Moisture content indication control	Certified MV Test Set
<b>Adjustment</b>	
Internal / External adjustment	Depending on the type of moisture analyzer, GLP report
Drying temperature adjustment	Three-point adjustment at defined temperatures, programmable values (equipment: GT105k-12/Z Control Thermometer)

<sup>1</sup> Barcode scanners, available as weighing instrument accessory, communicate with the instrument via RS232 interface exclusively.

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories

Antivibration Tables  
Moisture analyzer accessories  
Additional modules  
Barcode scanners  
Receipt Printer

Fingerprint Reader  
Protective cover for balances  
RS 232, RS 485 cables  
RS 232 cables (scale - printer)  
RS 232 – RS 485 Converter

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]

## Device dimensions

