

1.1.2.4 Low - Medium Power Thermal Sensors - Apertures to 35mm

30mW to 150W

Features

- Convection air cooled
- CW to 30W or 50W, intermittent to 150W
- Ø17.5mm and Ø35mm apertures
- Measure powers up to 4000W by short exposures to laser

30(150)A-BB-18



30(150)A-LP2-18



L50(150)A-BB-35
L50(150)A-PF-35



L50(150)A-LP2-35



Model	30(150)A-BB-18	30(150)A-LP2-18	L50(150)A-BB-35	L50(150)A-LP2-35	L50(150)A-PF-35
Use	General purpose	High power density and long pulse lasers	General purpose	High power density and long pulse lasers ^(b,c)	Short pulse lasers
Absorber Type	Broadband	LP2	Broadband	LP2	PF
Spectral Range μm	0.19 - 20	0.25 - 2.2	0.19 - 20	0.25 - 2.2	0.15-20
Absorption	>85%	>94% from 0.25 to 1.1 μm	>85%	>94% from 0.25 to 1.1 μm	>85%
Aperture mm	Ø17.5mm	Ø17.5mm	Ø35mm	Ø35mm	Ø35mm
Power Mode					
Power Range	30mW - 150W	30mW - 150W	100mW - 150W	100mW - 150W ^(b,c)	100mW - 150W
Maximum Intermittent Power W	150W for 1.5min, 100W for 2.2min, 30W continuous		150W for 1.5min, 100W for 2.5min, 50W continuous	For L50(150)A-LP2-35: 4000W for 0.4s exposure ^(b,c)	
Power Scales	150W / 30W / 3W	150W / 30W / 3W	150W / 50W / 5W	150W / 50W / 5W	150W / 50W / 5W
Power Noise Level	2mW	2mW	4mW	4mW	4mW
Maximum Average Power Density kW/cm^2	12 at 150W 20 at 30W	33 at 150W 50 at 30W	12 at 150W 17 at 50W	33 at 150W 50 at 50W	3
Response Time with Meter (0-95%) typ. s	1.2	1.2	2	2	2
Calibration Uncertainty $\pm\%$	1.9	1.9	1.9	1.9	1.9
Power Accuracy $\pm\%$	3	3 ^(a)	3	3 ^(a)	4 ^(d)
Linearity with Power $\pm\%$	1	1	1	1	1
Energy Mode					
Energy Range	20mJ - 100J	20mJ - 300J	40mJ - 300J	40mJ - 3000J	50mJ - 300J
Energy Scales	100J / 30J / 3J	300J / 30J / 3J	300J / 30J / 3J	3000J / 300J / 30J / 3J	300J / 30J / 3J
Minimum Energy mJ	20	20	40	40	50
Maximum Energy Density J/cm^2					Single ^(e) 10-50Hz ^(e)
<100ns	0.3	0.1	0.3	0.1	3 ^(f) 1.5
0.5ms	5	50	5	50	7 7
2ms	10	130	10	130	15 15
10ms	30	400	30	400	40 40
>300 ms	NA	NA	NA	See below ^(b,c)	NA NA
Cooling	convection / ballistic	convection / ballistic	convection / ballistic	convection / ballistic	convection / ballistic
Fiber Adapters Available (p. 93)	ST, FC, SMA, SC	ST, FC, SMA, SC	ST, FC, SMA, SC	ST, FC, SMA, SC	ST, FC, SMA, SC
Weight kg	0.3	0.3	0.35	0.35	0.35
Compliance	CE, UKCA, China RoHS	CE, UKCA, China RoHS	CE, UKCA, China RoHS	CE, UKCA, China RoHS	CE, UKCA, China RoHS
Version					
Part number	7Z02699	7Z02786	7Z02730	7Z02785	7Z02737

Notes: (a) Above 1.1 μm there is an additional calibration uncertainty of up to 2%.


Notes: (b) Long pulses (0.5 – 4s) can be used to measure power of high power lasers by measuring the energy of a short exposure. The StarBright, Juno, Juno+ and Centauri meters have a Pulsed Power mode where the user may specify the pulse width and get a reading directly in units of power for this short exposure energy measurement. See also page 85

Notes: (c) Powers up to 4000W can be measured. Recommended exposure times and 1/e² Gaussian beam diameters for very long pulses. Total energy for a series of measurements should not exceed 15kJ. Recommended time between shots 12s.

Notes: (d) Calibrated for 0.25 – 2 μm , 10.6 μm

Notes: (e) For 10-50Hz, derate as follows:
Wavelength Derate to value
1064nm Not derated
532nm Not derated
355nm 70% of stated value
266nm 15% of stated value
193nm 10% of stated value
Notes: (f) Damage threshold 1.5J/cm² for wavelengths <500nm

30(150)A-BB-18 / 30(150)A-LP2-18



L50(150)A-BB-35 / L50(150)A-LP2-35 / L50(150)A-PF-35

