

## designed for scientists



## C-MAG MS 4

/// Data Sheet

Magnetic stirrer without heating. With ceramic set-up plate which offers excellent chemical resistance.

- Powerful motor for stirring quantities of up to 5 I (H2O)
- Elevated control panel for protection against leaking liquids
- Speed range: 100 1500 rpm







@IKAworldwide



## designed for scientists

## **Technical Data**

Number of stirring positions	1	
Stirring quantity max. per stirring position (H2O) [I]	5	
Motor rating output [W]	1.5	
Direction of rotation	left	
Speed control	scale 0 - 6	
Speed range [rpm]	100 - 1500	
Set-up plate material	ceramic	
Set-up plate dimensions [mm]	100 x 100	
Dimensions (W x H x D) [mm]	150 x 105 x 260	
Weight [kg]	3	
Permissible ambient temperature [°C]	5 - 40	
Permissible relative humidity [%]	80	
Protection class according to DIN EN 60529	IP 21	
Voltage [V]	230 / 120 / 100	
Frequency [Hz]	50/60	
Power input [W]	30	





