

SALT CHECK



FEATURES

- Useful for Measuring Salt (%) of Food Solution
- Easy to Operate, Compact Size & Quick Reading
- Large Digital LCD display
- Electrical Conductivity Method Adopted
- Automatic Temperature Compensation
- **Automatic Calibration**

(* The instrument has a special function of Auto-Calibration.

In spite of any changes of surrounding environment, The unit is calibrated automatically

by G-WON Hitech's preset special programs.

Once calibration is not successful, Correct test results are not possible.

By Auto-Calibration, Customers can get accurate test results easily without doing calibration before every test.)

- Low Battery Sign appears
- As Measurement results are influenced by Temperature of Test Sample, You should pay high attention on the Temperature Changes. In order to get the most accurate test results, Three Kinds of Measuring Buttons are prepared as below :
 - "HOT" Button : Over 70°C
 - "NORMAL" Button : 20 ~ 30°C
 - "COLD" Button : Below 10°C

SPECIFICATIONS

MODEL	GMK-525N	GMK-545A	GMK-555N	GMK-555
MEASURING RANGES	0.00 % ~ 5.00 %	0.0 % ~ 5.0 %	0.0 % ~ 15.0 %	0.0 % ~ 10.0 %
REMARKS	Hot/Cold Temp. Select Buttons			Meas/Aver Buttons
RESOLUTION	0.01 %		0.1 %	

