

Hardness

Pencil Hardness Tester

■ Introduction:

BEVS1301 Pencil Tester complies with the requirements of ASTM D3363 and ISO15184 standard, through leaving a superficial trace on the dry coating film with a certain pencil hardness, the surface will be variably damaged by the hardest pencil to evaluate pass/fail or hardness. Recommend to apply on the smooth film surface. Use variety of different hardness pencils, the angle between pencil and the coated surface is 45°, scratch on the coated surface under a certain of force, the scratch resistance hardness of the coating is the pencil hardness which just scratched the coating.





■ Hardness Class:

♦ Hardness Increase

Harder

6B-5B-4B-3B-2B-B-Hb-F-H-2H-3H-4H-5H-6H

Mitsubishi pencils are available upon request



- ◆ Pressure of pencil tip: 1000/750/500g
- ◆The angle between pencil and film surface is 45°
- ◆Three points are touched on the tested surface (roller, pencil tip)



■ Order Information:

BEVS 1301/500 Pencil Hardness Tester (500g)
BEVS 1301/750 Pencil Hardness Tester (750g)
BEVS 1301/1000 Pencil Hardness Tester (1000g)