Q

1

Laboratory Deionized Water Machine 10L/H

- TOB-DBW-SYS-10L/H Deionized Water Machine is a lab water purifier widely used for Electronic industry, pharmaceutical industry, chemical industry etc. Laboratory Ultrapure water preparation.
- Item No.: TOB-DBW-SYS-10 •
- Order(Moq):1set •
- Payment:L/C,T/T,Western Union, • Paypal
- Product Origin: China •
- Shipping Port:XIAMEN •
- Lead Time:7days

Product Detail

10L/H Laboratory Deionized Water Machine For Lithium Battery Mixing Water Preparation





SPECIFICATIONS


1 TOB-DBW-SYS-10L/HDeionized Water Machineis a lab water purifier widely used for Electronic industry, pharmaceutical industry, chemical industry etc. Laboratory Ultrapure water preparation. 2 ThisDeionized Water Machineadopts reverse osmosis membrane (RO) membrane as the core, supplemented by multi-stage pretreatment of membrane type pure water machine, using the current international advanced reverse osmosis technology and Mixed bed desalination process to prepare ultrapure water.

3 For Lithium battery lab research, theDeionized Wateris used for battery cathode materials mixing with water to improve lithium battery performance.

4 ThisDeionized Water machinecan also be used for lead-acid battery and solar cell producing and research.

| Model | Laboratory Deionized Water Machine TOB-DBW-SYS-10 |
|--------------------------|---|
| Source voltage | AC 220V/110V, 50HZ |
| Power | 30W |
| Warranty | One year limited warranty and lifetime support |
| Making water quantity | 10L/H, Customized |
| Output water quality | Ratio of desalinization : >99.99% |
| | Conductivity : < 0.01-0.056us.cm |
| | Electrical resistivity : 10-18MΩ.cm |
| | Sio2≤0.01 |
| Structure | Status online display, Microcomputer automatic control system of water process, |
| | Displays Power supply, water, flushing, filled with water, lack of water, |
| | with Low voltage protection, high voltage protection. |
| | Water shortage, water full, the system automatically stop |
| | Automatic and simple operation. |
| Dimension(L*W*H) | 450*350*650mm |
| Weight | 40kg |

PRODUCT DISPLAY



Simple connection for deioinzed water machine

Accessories for Deionized water machine



PACKAGE AND SHIPPING

1 Standard exported package : Internal anticollision protection, external export wooden box package

2 Shipping by express, by air, by sea according to customer's requirements to suggest the most suitable shipping mode

3 Responsible for the damage during shipping process, change the damage part for free

4 Supply with suitable voltage input and power plug according to customer's country requirements.

5 Supply with CO, ECO, FORM A, FORM E and any other original certificate for import custom clearance and tax relief.

SERVICES

1 We supply machines with battery technology support.

2 We can also supply a full set of materials for lithium battery including polymer battery, cylinder battery, mobile phone battery, EV battery.

3 We can also supply a full set of lithium battery equipment for lab research, pilot scale research and production line.

4 We can also supply a full set of battery technology for battery design, research and producing.