


Taber® 710 Multi-Finger Scratch/Mar Tester



Taber® 710 Multi-Finger Scratch/Mar Tester

Taber® 710 Multi-Finger Scratch/Mar Tester

The design of Taber's Multi-Finger Scratch / Mar Tester is based on the apparatus described in automotive specifications (including Ford BN 108-13; General Motors GMN3943; and Daimler-Chrysler LP-463DD-18-01), which is commonly referred to as a five-finger (five-arm) scratch & mar tester.

The instrument includes a pneumatically driven, moveable sledge to which the test sample is mounted. The sledge moves in a linear fashion, and is operated by a control knob for one or multiple pass testing. An electronic timer displays the rate of speed, which can be controlled by reducing or increasing air pressure.

A gantry supports five independent splined-fingers, which provide a constant, vertical load on interchangeable scratch pins (1.0mm or 7.0mm diameter hemisphere). The gantry system includes a handle to raise and lower the arms. In addition, five support rests are incorporated to allow one or more arms to be moved to an upright, rest position such that the arm does not contact the specimen during testing.

Individual weights of varying loads mount to the top of each arm finger to exert a standard force on the surface of the test material. Each instrument includes a weight set of 2N, 3N, 4N, 5N, 6N, 7N, 10N, 15N and 20N loads. Other weights are available for 8N, 13N, 18N and 25N.

Although flat specimens up to 22mm thick are normally tested, the 'free-floating' arms fingers enable you test evaluate slightly contoured specimens provided they are rigid or adequately supported. A spring-loaded specimen holder is standard and can be mounted to the end or side of the moveable sledge for greater flexibility. To mount contoured specimens, an optional set of 'moveable' hold-down clamps is available.

Each unit is supplied complete with:

- Spline Shaft Finger Assembly (5 each)
- Scratch Tip, 1.0 mm Diameter Hemisphere (5 each)
- Mar Tip, 7.0 mm Diameter Hemisphere (5 each)
- 9-Piece Weight Set
- Electronic Timer with Digital Display
- Adjustable Specimen Clamp (set of 2)
- Quick Disconnect Socket for Air Supply
- Hex Wrench

Washability, Brushability and Abrasion Testers

Improved mechanical resistance is part of today's quality requirements. One important criteria for assessing this feature is abrasion resistance. Depending on the nature and purpose of the product, various testing methods are available.

There are testing methods are related to the "abrasion by friction" concept. Others are based on the projection of abrasive particles on to the test specimen. These techniques provide valuable information about materials and processes. To meet industry's growing needs for research and control,

Elcometer develops, manufactures and supplies a range of instruments designed for wear resistance tests. Standardised or conventional, these tests are widely used for numerous applications.

Model	Description	Part Number
Elcometer 710	Multi-Finger Scratch/Mar Tester	ST980710

Related Products



Elcometer Taber 5130

Often referred to as the industry standard the Taber rotary abrasers are written in to many standards throughout the world in many different industries. A sample of the product is positioned onto a rotating table and the user's choice of abrading wheels then apply the unique 'tearing' or abrasion pattern.



Elcometer Taber 5700

This linear abraser uses a free floating head to follow the contours of the sample under test - making it an ideal choice for abrasion testing of any curved surface.

ENGLAND

Elcometer Instruments Ltd
Edge Lane
Manchester M43 6BU

Tel: +44 (0)161 371 6000
Fax: +44 (0)161 371 6010
e-mail: sales@elcometer.com
www.elcometer.com

USA

Elcometer Inc
1893 Rochester Industrial Drive
Rochester Hills Michigan 48309

Tel: +1 248 650 0500
Toll Free: 800 521 0635
Fax: +1 248 650 0501
e-mail: inc@elcometer.com
www.elcometer.com

CANADA

Elcometer Ltd
PO Box 622, 401 Ouelette Avenue
Windsor, Ontario N9A 6N4

Tel: +1 248 650 0500
Toll Free: 800 521 0635
Fax: +1 248 650 0501
e-mail: ca_info@elcometer.com
www.elcometer.com

ASIA & THE FAR EAST

Elcometer (Asia) Pte Ltd
896 Dunearn Rd
Sime Darby Centre #3-09
Singapore 589472,
Republic of Singapore

Tel: +65 6462 2822
Fax: +65 6462 2860
e-mail: asia@elcometer.com
www.elcometer.com

BELGIUM

Elcometer SPRL
Rue Vallée 13
B-4681 Hermalle /s Ardenteau

Tel: +32 (0)4 379 96 10
Fax: +32 (0)4 374 06 03
e-mail: be_info@elcometer.be
www.elcometer.be

FRANCE

Elcometer SARL
BP 8-Bou
60 Rue de la Petite Levée
45430 Chécy

Tel: +33 (0)2 38 86 33 44
Fax: +33 (0)2 38 91 37 66
e-mail: fr_info@elcometer.fr
www.elcometer.fr

GERMANY

Elcometer Instruments GmbH
Himmlingstraße 18
D-73434 Aalen

Tel: +49 (0)7366 91 92 83
Fax: +49 (0)7366 91 92 86
e-mail: de_info@elcometer.de
www.elcometer.de