



# **Spectrophotometer (HSCD Series)**

## **Brochure**

### **Global Office of Lisun Electronics Inc.**

<http://www.Lisungroup.com>

Lisun Group (Hong Kong) Limited

Add: Room 803, Chevalier House, 45-51 Chatham Road South, Tsim Sha Tsui, KL, HK

Tel: 00852-68852050 Fax: 00852-30785638

Email: SalesHK@Lisungroup.com

Lisun Electronics (Shanghai) Co., Ltd

Add: 113-114, No. 1 Building, Nanxiang Zhidi Industry Park, No. 1101, Huyi Road, Jiading District, Shanghai, 201802, China

Tel: +86(21)5108 3341 Fax: +86(21)5108 3342

Email: SalesSH@Lisungroup.com

Lisun Electronics Inc. (USA)

Add: 445 S. Figueroa Street, Los Angeles, CA 90071, U.S.A.

Email: Sales@Lisungroup.com

Lisun China Factory

Add: NO. 37, Xiangyuan Road, Hangzhou City, Zhejiang Province, China

Tel: +86-189-1799-6096

Email: Engineering@Lisungroup.com

**Leader in Lighting & Electrical Test Instruments**

Rev. 10/18/2019

# Spectrophotometer

## product models



**HSCD-680**



**HSCD-700**



**HSCD-710**



**HSCD-750**




**HSCD-760**

## Brief Introduction


- Our device adopts internationally agreed observe condition D/8 (Diffused lighting, 8 degrees observe angle) and SCI (specular reflection included) / SCE (specular reflection excluded).

It could be used for color matching for many industries and widely used in painting industry, textile industry, plastic industry, food industry, building material industry and other industries for quality control.





- **Camera view to catch the testing area**

In previous measurement instrument, we can only aim at the testing area approximately, and this may cause errors. Our spectrophotometers include a camera in our optical system, and the user can clearly see the tested area to avoid measurement errors.




- **Uses CLEDs light source – spectrally balanced LED light source**

LED light source that has balanced intensity across visible spectrum avoids the spectral deficiency in certain parts of the spectrum in common white LEDs, and guarantees the speed of the measurement and the accuracy of the results. This research finding has been published in national leading, SCI included optical journal, Chinese Optics Letter.




- **ETC Every Time calibration technology**

Currently, most instruments use standard white boards for calibration. When white board is damaged, the instrument's accuracy or precision will no longer be guaranteed. In CHN Spec's spectrophotometers, it uses innovative ETC(Every Test Calibration); standard white board is included in the optical system, and therefore has reliable accuracy and repeatability in every measurement.



- **Matching color analysis software**


Our spectrophotometer has the color management software, which is applicable in various industries' quality control and management of color data. It turns color into numerical data, compares color differences, generates measurement reports, provides measurement data under different color spaces and customizes color management for each customer.



- **Automatic gloss compensation technology**

Different gloss, or different instrument's lighting or observation conditions will


largely affect the measurement of color. The automatic gloss compensation technology guarantees the accuracy of color measurement data for surfaces of different gloss. This research finding is published in international leading, SCI included journal, Optic.



Different gloss will cause the different measurement

- **Innovative light splitting SCS optical engine**

Adopt innovative single-grating-double-beam light splitting system: SCS optical engine, creates the best measurement repeatability for portable spectrophotometers in the industry, and guaranteed accurate measurement of surface color of materials.



- **The most complete and color indicators compares with similar instruments.**

Comparing with similar products, our spectrophotometers offer the most complete, 28 kinds of standard light sources for lighting conditions and 40 measurement color value indicators; It can also customize measurement methods according to your requirement, and satisfy all your color measurement needs.

### Technical Data

| Type                  | HSCD-680                                                                                                                                                                                                                                                                               | HSCD-700 | HSCD-710 | HSCD-750 | HSCD-760 |
|-----------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------|----------|----------|----------|
| Measurement condition | Observation angle: 2°/10°<br>Illumination: d/8(Diffused lighting, 8 degrees observe angle)、SCI (specular reflection included)/SCE (specular reflection excluded)simultaneous measurement 。 (conform to CIE No.15、ISO 7724/1、ASTME1164、DIN 5033 Teil7、 JIS Z8722 Condition c standards) |          |          |          |          |
| Size of               | Φ40mm,Avian diffused reflection surface coating                                                                                                                                                                                                                                        |          |          |          |          |

| Type                      | HSCD-680                                                                                                                                                                                                                                                     | HSCD-700                                                                                                                                                 | HSCD-710 | HSCD-750         | HSCD-760                                    |
|---------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|----------|------------------|---------------------------------------------|
| integrating sphere        |                                                                                                                                                                                                                                                              |                                                                                                                                                          |          |                  |                                             |
| Illumination Light source | CLEDs(Full band balanced LED light source)                                                                                                                                                                                                                   |                                                                                                                                                          |          | Pulse Xenon Lamp | CLEDs (Full band balanced LED light source) |
| Sensor                    | dual light path sensor array                                                                                                                                                                                                                                 |                                                                                                                                                          |          |                  |                                             |
| Wavelength Range          | 400-700nm                                                                                                                                                                                                                                                    |                                                                                                                                                          |          | 360-740nm        | 400-700nm                                   |
| Wavelength interval       | 10nm                                                                                                                                                                                                                                                         |                                                                                                                                                          |          |                  |                                             |
| Half spectral width       | 5nm                                                                                                                                                                                                                                                          |                                                                                                                                                          |          |                  |                                             |
| Reflectivity range        | 0-200%                                                                                                                                                                                                                                                       |                                                                                                                                                          |          |                  |                                             |
| Reflectivity resolution   | 0.01%                                                                                                                                                                                                                                                        |                                                                                                                                                          |          |                  |                                             |
| Measurement light source  | A,C,D50,D55,D65,D75,F1,F2,F3,F4,F5,F6,F7,F8,F9,F10,F11,F12,DLF,TL83,TL84,NBF,U30,CWF                                                                                                                                                                         |                                                                                                                                                          |          |                  |                                             |
| Data being displayed      | SPD distribution/data, sample's color values, color difference values/graph, pass/fail results, color error tendency, color simulation, display measurement area, history data color simulation , manual input standard sample , generate measurement report |                                                                                                                                                          |          |                  |                                             |
| Measurement time interval | 2 seconds                                                                                                                                                                                                                                                    |                                                                                                                                                          |          |                  |                                             |
| Measurement time          | 2S                                                                                                                                                                                                                                                           | 0.5S                                                                                                                                                     |          | 2S               | 0.5S                                        |
| Color space               | CIE-L*a*b, L*C*h, L*u*v, XYZ, Yxy, Reflective                                                                                                                                                                                                                | CIE-L*a*b, L*C*h, L*u*v, XYZ, Yxy, Reflective, Hunterlab, Munsell MI, CMYK, RGB, HSB                                                                     |          |                  |                                             |
| Color difference formulas | $\Delta E^*ab$ , $\Delta E^*CH$ , $\Delta E^*uv$ , $\Delta E^*cmc(2:1)$ , $\Delta E^*cmc(1:1)$ , $\Delta E^*94$ , $\Delta E^*00$                                                                                                                             | $\Delta E^*ab$ , $\Delta E^*CH$ , $\Delta E^*uv$ , $\Delta E^*cmc(2:1)$ , $\Delta E^*cmc(1:1)$ , $\Delta E^*94$ , $\Delta E^*00$ , $\Delta Eab$ (Hunter) |          |                  |                                             |
| Other                     | WI(ASTM E313-10,ASTM E313-73,CIE/ISO, AATCC, Hunter,                                                                                                                                                                                                         |                                                                                                                                                          |          |                  |                                             |

| Type                       | HSCD-680                                                                                                                                                            | HSCD-700                                                                                                                                        | HSCD-710                                | HSCD-750 | HSCD-760                                               |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------|----------|--------------------------------------------------------|
| colorimetric indices       | Taube Berger, Ganz, Stensby); YI(ASTM D1925, ASTM E313-00,ASTM E313-73); Tint(ASTM E313,CIE,Ganz)<br>Metamerism index Milm, Stick color fastness, Color fastness    |                                                                                                                                                 |                                         |          |                                                        |
|                            |                                                                                                                                                                     | ISO luminance, 8 gloss, A density, T density, M density, E density                                                                              |                                         |          |                                                        |
| Repeatability              | light splitting reflectivity: standard deviation within 0.08%                                                                                                       |                                                                                                                                                 |                                         |          |                                                        |
|                            | Color values:<br>ΔE*ab<= 0.03(After calibration, standard deviation of 30 measurements on test white board, 5 second intervals), Maximum :0.05                      | color values;<br>ΔE*ab<= 0.03(After calibration, standard deviation of 30 measurements on test white board, 5 second intervals), Maximum : 0.05 | color values: ΔE*ab <=0.02,Maximum:0.04 |          | Chromaticity values:<br>ΔE*ab<= 0.015<br>Maximum :0.03 |
| Battery capacity           | rechargeable, 10000 continuous tests, 7.4V/6000mAh                                                                                                                  |                                                                                                                                                 |                                         |          |                                                        |
| Interface                  | USB                                                                                                                                                                 |                                                                                                                                                 |                                         |          |                                                        |
| Data storage               | 20000 test results                                                                                                                                                  |                                                                                                                                                 |                                         |          |                                                        |
| Light source longevity     | 5 years, 1.5 million tests                                                                                                                                          |                                                                                                                                                 |                                         |          |                                                        |
| Inter-instrument agreement | ΔE*ab within 0.2(BCRA color charts II, average of the 12 charts)                                                                                                    |                                                                                                                                                 |                                         |          |                                                        |
| Size                       | 181*73*112mm(L*W*H)                                                                                                                                                 |                                                                                                                                                 |                                         |          |                                                        |
| Weight                     | about 550g(does not include battery's weight)                                                                                                                       |                                                                                                                                                 |                                         |          |                                                        |
| Display                    | True color screen that includes all colors                                                                                                                          |                                                                                                                                                 |                                         |          |                                                        |
| Work temperature range     | 0~45℃, relative humidity 80% or below( at 35℃ ),no condensation                                                                                                     |                                                                                                                                                 |                                         |          |                                                        |
| Storage temperature range  | -25℃ to 55℃, relative humidity 80% or below(at 35℃ ),no condensation                                                                                                |                                                                                                                                                 |                                         |          |                                                        |
| Standard accessories       | DC adapter, Lithium battery, manual, color management software, drive software, electronic manual, color management guide, USB cable, black/white calibration tube, |                                                                                                                                                 |                                         |          |                                                        |

| Type                  | HSCD-680                                                                                            | HSCD-700 | HSCD-710 | HSCD-750             | HSCD-760                |
|-----------------------|-----------------------------------------------------------------------------------------------------|----------|----------|----------------------|-------------------------|
|                       | protective cover, spire lamella, portable bag, electronic color charts, measurement and test report |          |          |                      |                         |
| Optional              | powder molding device, micro printer                                                                |          |          |                      |                         |
| Color matching system | not match                                                                                           | match    |          |                      |                         |
| UV light source       | without UV light source                                                                             |          |          | With UV light source | without UV light source |

## Application

