

TUC series

Multifunctional Ultrasonic Cleaner With LCD Display @TUC Series

- With large LCD display to show the precise time, temperature, power level
- Time setting with 1-99 minutes and built-in heating to 60°C, adjustable power range of 10%~100%.

- Built-in "sound insulation paste" keep this series with low noise
- With sweep function & degas function
- Humanized carrying handle and drain valve for whole models
- Memory function will automatically save the most recently used setup parameters for next use.
- With sleeping mode to keep electrical energy saving

Selling points for this series:

- 1. Adjustable power
- 2. Low noise
- 3. Sweep function
- 4. Degas function
- 5. Heating function
- 6. Adjustable time
- 7. Memory function
- 8. Sleeping mode

A full set including:

- 1xultrasonic cleaner
- 1xSUS cleaning basket
- 1xSUS lid
- 1×power cord
- 1xEnglish user manual
- 1xcarton box

| Model | TUC-32 | TUC-48 | TUC-45 | TUC-65 | TUC-70 | TUC-100 | TUC-150 | TUC-200 | TUC-220 |
|----------------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|---------------------------|
| Ultrasonic Power(W)- Max | 120 | 120 | 180 | 180 | 240 | 240 | 360 | 360 | 480 |
| Ultrasonic Power setting-% | 10%-100% (step by 10%) |
| Heating Power(W)- Max | 100 | 100 | 200 | 200 | 500 | 500 | 500 | 500 | 500 |
| Capacity (L)- Max | 3.2 | 4.8 | 4.5 | 6.5 | 7 | 10 | 15 | 20 | 22 |
| Tank Size(L*W*H)- MM | 240*135*100 | 240*135*150 | 300*150*100 | 300*150*150 | 300*240*100 | 300*240*150 | 330*300*150 | 330*300*200 | 500*300*150 |

| TUC-300 | TUC-450 |
|---------------|--------------|
| 600 | 720 |
| 1096-10096 | 10%-100% |
| (step by 10%) | (step by 109 |
| 500 | 1000 |
| 30 | 45 |

500*300*200 500*300*300

| Transducer Qty(PCS) | | 2 | 2 | 3 | 3 | Household ditrasonic Cleaner @CE Series | 6 | 6 | 8 | | |
|------------------------------------|------|-----|-----|-----|-----|---|-----|-----|-----|--|--|
| Drain Valve(Yes or No) | | Yes | Yes | Yes | Yes | Yes Denture Ult Yes inic Cleaner @CE Series Ultrasonic Contact Lens | Yes | Yes | Yes | | |
| Carrying Handle(Yes or No) | | Yes | Yes | Yes | Yes | Yes Cleaner @CE Series Yes Bench Top Stainless Steel Ultrasonic Cleaner | Yes | Yes | Yes | | |
| Ultrasonic Freq(KHz) | 40 | 40 | | | | | | | | | |
| Temperature Setting(°C)- Max | 60 | | | | | | | | | | |
| Timer Setting(MINS) | 1-99 | | | | | | | | | | |