

Velcro Fatigue Tester HTF-009



Detailed Description

Through the apparatus to achieve Velcro (hook & loop) to repeated stripping and peeling after a certain times. Cut the sample into 75x 20mm with press it with the wheel to be fitted completely. Use tensile machine (another purchase) to measure its peeling strength (AS) and shear strength (PA)

Specifications:

Trolley diameter:

- Top round: $\Phi 162.5\text{mm}$

- Base round: $\Phi 160\text{mm}$

Trolley Width: 80mm

Trolley speed: 72rpm

Counter: LCD, 0~999,999

Dimension: 45×55×57cm

Weight: 5kg

Power: 1 ϕ AC220V, 3A

Standards: DIN-3415, SATRAPM123