Choose language 🛛 🗙



(/)

search

9

Home (/) >> PRODUCT (http://www.hssdgroup.com/PRODUCT/) >> Specimen Making Machine (http://www.hssdgroup.com/PRODUCT/Broaching\_Machine/)





## VU-1S Manual Charpy Impact Specimen Broacher

Product description:

1.Application VU-1S Manual Notch Cutting Machine for Impact Specimen is used to cut notch in the impact test for petroleum chemical industry, metallurgy, boiler and pressure vessel, steel plate, steel



(http://www.hssdgroup.com/PROL/UttlpII/@om/pressegion\_presser/PROL/UttlpII/@om/pressegion\_presser/PROL/UttlpII/@om/pressegion\_presser/PROL/UttlpII/@om/pressegion\_presser/PROL/UttlpII/@om/pressegion\_presser/PROL/UttlpII/@om/pressegion\_presser/PROL/UttlpII/@om/pressegion\_presser/PROL/UttlpII/@om/pressegion\_presser/PROL/UttlpII/@om/pressegion\_presser/PROL/UttlpII/@om/pressegion\_presseg

Share With:

We're here to help: Easy ways to get the answers you need.

Send E-mail (mailto:Louis@hssdtest.com)

Chat Now (skype:sales02@hssdtest.com?chat)

## HST HST GROUP

(/)

Focus In Material Test

VU-1S Manual Notch Cutting Machine for Impact Specimen is used to cut notch in the impact test for petroleum chemical industry, metallurgy, boiler and pressure vessel, steel plate, steel pipe, wind power generation, hardware, metal, casting, pump, valve, solar, ordnance, fasteners, diesel engine, electric power, iron tower, railway, ship, machinery manufacturing, automotive, aerospace, physical and chemical laboratory, scientific Research

## 2. Standards:

ASTM E23-02a, EN10045, ISO148, ISO083, GB229-2007

## 3. Main Technical Specifications:

Shape of sample notch

Sample size

Cutting mode Broach material Max. Dimension Weight V-shape(2 mm) or U-shape (2mm), only choose one 10×10×55mm (or 10×10×7.5mm , 10×10×2.5mm) Manual W18Cr4V 350×350×600mm 100kg