

Cat.No.0190-04

Concentration Meter for Soba and Udon Model SK-202R



Model

SK-202R

Concentration: Soup 0 to 56%, Salt water 0 to 28%

Object to be measured: soup and salt water

Specifications

Model	Cat. No.	Scale (Brix)	Min. Scale	Auto Temperature Correction (temp. range)	Grip Dia.	Length	Weight
SK-100R	0180-00	Brix 0.0 to 32.0%	Brix 0.2%	10 to 30°C	Approx. Ø29	Approx. 170mm	Approx. 105g
SK-101R	0181-00	Brix 28.0 to 62.0%	Brix 0.2%	10 to 30°C	Approx. Ø29	Approx. 160mm	Approx. 105g
SK-102R	0182-00	Brix 0.0 to 18.0%	Brix 0.1%	10 to 30°C	Approx. Ø29	Approx. 195mm	Approx. 120g
SK-104R	0184-00	Brix 0.0 to 10.0%	Brix 0.1%	10 to 30°C	Approx. Ø29	Approx. 195mm	Approx. 120g
SK-106R	0186-00	Brix 58.0 to 92.0%	Brix 0.2%	10 to 30°C	Approx. Ø29	Approx. 150mm	Approx. 100g
SK-107R	0187-00	Brix 45.0 to 82.0%	Brix 0.5%	10 to 30°C	Approx. Ø29	Approx. 145mm	Approx. 100g
SK-109R	0189-00	Brix 0.0 to 50.0%	Brix 0.5%	10 to 30°C	Approx. Ø29	Approx. 155mm	Approx. 100g
SK-200R	0190-00	Salt concentration 0.0% to 28.0%	Salt concentration 0.2%	10 to 30°C	Approx. Ø29	Approx. 170mm	Approx. 105g
SK-201R	0190-02	Soup concentration 0.0 to 32.0%	Soup concentration 0.2%	---	Approx. Ø29	Approx. 185mm	Approx. 115g
		Baume deg, of brine water 0.0 to 10.0	Baume deg, of brine water 0.5				
SK-202R	0190-04	Soup concentration 0 to 56% Salt water 0 to 28%	Soup concentration 1% Salt water 1%	---	Approx. Ø29	Approx. 145mm	Approx. 100g

		28%					
--	--	-----	--	--	--	--	--

NB: Brix(%) scale is indicated in percentage of sucrose in 100g of sucrose solution. Conversion chart is required for the quantitatively measurement of concentration of liquid solutions mainly composed other substance.

Standard accessories	
Manual, dropper one screw driver, one wipe-out cloth, carrying case, distilled water (applicable for SK-100R, 102R, 104R, 109R, 201R and 202R), oil for adjustment, block for adjustment 1 pc. for each(applicable for SK-106R and 107R), saturation salt water (applicable for SK-101R)	
Consumables	
No. 0180-10 Cover Plate (usable for SK-R Series Refractometers)	
Materials	
Main unit	: Aluminum alloy
Prism	: Optical glass
Cover plate	: Polycarbonate
Grip, Adjusting screw	: Synthetic rubber

SK-100R/102R/104R/109R/200R/201R/202R	SK-101R	SK-106R/107R
---------------------------------------	---------	--------------



