



Mouth-actuated Catapult Endurance Tester For Toys GT-M04-1

Product Introduction

Application:

This Toys testing equipment is used to test mouth-actuated projectile toys' blowing resistant properties.

Standards:

EN-71-1 section 8.17.1

Test principle

The catapult was placed into the mouth-actuated projectile toys. Add pressure of $13.8\text{kPa} \pm 5\%$ on the mouthpiece, lasts for 5 seconds, test a total of 10 times. Detecting whether the projectile through the mouthpiece.

Key Specifications

Standards:

EN-71-1 section 8.17.1

Test principle

The catapult was placed into the mouth-actuated projectile toys. Add pressure of $13.8\text{kPa} \pm 5\%$ on the mouthpiece, lasts for 5 seconds, test a total of 10 times. Detecting whether the projectile through the mouthpiece.

Key Specifications

Model	GT-M04-1
Test air pressure	13.8 Kpa
Hold time	5s
Testing times	10 times
Power Supplier	AC 220V, 50HZ
Accessories	Tube gripper 3pcs